



## Luminaire

# Rotao60

227-2B0I-10GGD/840, W +  
00-00379, W



The designer circular luminaire Rotao60 comes in a large number of diameters, thanks to which it fits well into various social and commercial spaces. You can also use it to decorate your living room or a meeting room. If you combine the luminaire with microprismatic optics, its efficacy can be surprising even in an office. Pendant versions of the Rotao60 luminaire with a diameter of up to 800 mm are suspended on suspension wires which converge into a single ceiling cup, while larger diameters are suspended on wires that run perpendicular to the ceiling.

## Technical drawing



|                           |                      |
|---------------------------|----------------------|
| Type of installation      | Suspended            |
| Light distribution        | Direct               |
| Luminaire shape           | Circular             |
| Colour of the luminaires  | White                |
| Material                  | Aluminium            |
| Lifetime                  | L80/B20 50 000 hours |
| Warranty                  | 60 months            |
| Description of luminaires | Luminaire suspended  |
| Dimensions                | ø 1140 mm × 65 mm    |
| Weight                    | 10.1 kg              |
| Light source              | LED MODUL            |

|                                   |                   |
|-----------------------------------|-------------------|
| Type of optical system            | Microprisma       |
| Luminous flux                     | 6000 lm ± 10 %    |
| Colour Temperature                | 4000 K cool white |
| Luminous efficacy                 | 94 lm/W           |
| MacAdam Light source              | 3                 |
| Colour rendering index            | 80                |
| UGR max. X=4H<br>Y=8H, ρ=70,50,20 | 20.4              |

## Curve



Luminaire power input 63.6 W  $\pm$  10 %

Connection of the luminaires DALI dimmable

Electrical voltage 220-240V

Frequency 50/60Hz

⊕ CE IP 20

## Downloads

Installation instructions



Photos

