



## Luminaire

# Rotao60

227-5B1K-10GGD/830, B



The designer circular luminaire Rotao60 comes in a large number of diameters, thanks to which it fits well into various social and commercial spaces. You can also use it to decorate your living room or a meeting room. If you combine the luminaire with microprismatic optics, its efficacy can be surprising even in an office. Pendant versions of the Rotao60 luminaire with a diameter of up to 800 mm are suspended on suspension wires which converge into a single ceiling cup, while larger diameters are suspended on wires that run perpendicular to the ceiling.

## Technical drawing



|  |                      |
|--|----------------------|
| Type of installation                   | Suspended            |
| Light distribution                     | Direct-indirect      |
| Luminaire shape                        | Circular             |
| Colour of the luminaires               | Black                |
| Material                               | Aluminium            |
| Lifetime                               | L80/B20 50 000 hours |
| Warranty                               | 5 years              |
| Description of luminaires              | Luminaire suspended  |
| Dimensions                             | ø 1140 mm × 65 mm    |
| Weight                                 | 9 kg                 |
| Light source                           | LED MODUL            |
| Type of optical system                 | Opal diffuser        |
| Luminous flux*                         | 8100 lm              |
| Colour Temperature                     | 3000 K warm white    |
| Luminous efficacy                      | 96 lm/W              |
| MacAdam Light source                   | 3                    |
| Colour rendering index                 | 80                   |
| UGR max. X=4H<br>Y=8H, $\rho=70,50,20$ | 23                   |

## Curve



Luminaire power input\* 84.8 W

Connection of the luminaires DALI

Electrical voltage 220-240V

Frequency 50/60Hz

⊕ CE IP 20

\*±10 %

## Downloads

Installation instructions



Photos

